

Accredited

Not accredited

Thermometers

Product	Range	Best CMC Uncertainty
Pt 100 - sensors	-80 °C to 250 °C	0,07 K
Thermocouple sensors	-80 °C to 1000 °C	0,1 K
Temperature baths	-80 °C to 250 °C	
Thermocycler	+30 °C to +95 °C	0,1 K
Dry block	-80 °C to 250 °C	
Infrared temperature devices	-80 °C to 400 °C	
Portable temperature devices	-80 °C to 1000 °C	0,07 °C
Liquid in glass	-80 °C to 250 °C	0,07 °C

Dataloggers

Product	Range	Best CMC Uncertainty
External temperature sensor	-80 °C to 1000 °C	0,07 °C
Internal temperature sensor	- 40 °C to 140 °C	
Humidity	20 % rH to 90 % rH (at 20 ° to 40 °C)	

Simulators

Product	Range	Best CMC Uncertainty
Pt100 simulator	EN/IEC 60751	0,02 °C
Thermocouple simulator	EN/IEC 60584	0,06 °C