

Melting Point version of Periodic Table

Element	Element symbol	Atomic number	Melting point in °C	Boiling point in °C
Actinium	Ac	89	1050	3198
Aluminium	Al	13	660.32	2519
Americium	Am	95	1176	2011
Antimony	Sb	51	630.63	1587
Argon	Ar	18	-248.609	-246.053
Arsenic	As	33	subl.616	subl.616
Astatine	At	85	302	336.95
Baryum	Ba	56	727	1897
Berkellium	Bk	97	996	
Beryllium	Be	4	1287	2471
Bismuth	Bi	83	271.4	1564
Bohrium	Bh	107		
Boron	B	5	2075	4000
Bromine	Br	35	-7.2	58.8
Cadmium	Cd	48	321.07	767
Caesium	Cs	55	28.44	691
Calcium	Ca	20	842	1484
Californium	Cf	98	900	
Carbon	C	6	3550	4827
Cerium	Ce	58	799	3443
Chlorine	Cl	17	-101.5	-34.04
Chromium	Cr	24	1907	2671
Cobalt	Co	27	1495	2927
Copernicium	Cn	112		
Copper	Cu	29	1084	2562
Curium	Cm	96	1325	
Darmstedtium	Ds	110		
Dubnium	Db	105		
Dysprosium	Dy	66	1412	2567
Einsteinium	Es	99	860	
Erbium	Er	68	1529	2868
Europium	Eu	63	822	1596
Fermium	Fm	100	1527	
Fleворium	Fl	114		
Fluorine	F	9	-219.67	-188.12
Francium	Fr	87	27	677
Gadolinium	Gd	64	1313	3273
Gallium	Ga	31	29.776	2204
Germanium	Ge	32	938.25	2833
Gold	Au	79	1064.18	2856
Hafnium	Hf	72	2233	4603
Hassium	Hs	108		
Helium	He	2	-272.2	-268.93
Holmium	Ho	67	1472	2700
Hydrogen	H	1	-259.1	-252.76
Indium	In	49	156.6	2072
Iodine	I	53	113.7	184.4
Iridium	Ir	77	2446	4428
Iron	Fe	26	1538	2861
Krypton	Kr	36	-157.36	-153.34
Lanthanum	La	57	920	3464
Lawrencium	Lr	103		
Lead	Pb	82	327.46	1749
Lithium	Li	3	180.5	1342
Livermorium	Lv	116		
Lutetium	Lu	71	1663	3402
Magnesium	Mg	12	650	1090
Manganese	Mn	25	1246	2061
Meitnerium	Mt	109		

Element	Element symbol	Atomic number	Melting point in °C	Boiling point in °C
Mendelevium	Md	101	827	
Mercury	Hg	80		
Molybdenum	Mo	42	2623	4639
Moscovium	Mc	115		
Neodymium	Nd	60	1016	3074
Neon	Ne	10	-248.609	-246.653
Neptunium	Np	93	644	3902
Nickel	Ni	28	1455	2913
Nihonium	Nh	113		
Niobium	Nb	41	2477	4744
Nitrogen	N	7	-210	-195.798
Nobelium	No	102		
Oganesson	Og	118		
Osmium	Os	76	3033	5012
Oxygen	O	8	-218.79	-182.95
Palladium	Pd	46	1654.8	2963
Phosphorus	P	15	44.15	280.5
Platinum	Pt	78	1768.2	3825
Plutonium	Pu	94	640	3228
Polonium	Po	84	254	962
Potassium	K	19	63.5	759
Praseodymium	Pr	59	931	3520
Promethium	Pm	61	1042	3000
Protactinium	Pa	91	1572	
Radium	Ra	88	696	1140
Radon	Rn	86	-71	-61.7
Rhenium	Re	75	3185	5596
Rhodium	Rh	45	1964	3695
Roentgenium	Rg	111		
Rubidium	Rb	37	39.3	688
Ruthenium	Ru	44	2334	4150
Rutherfordium	Rf	104		
Samarium	Sm	62	1072	1794
Scandium	Sc	21	1541	2836
Seaborgium	Sg	106		
Selenium	Se	34	221	685
Silicon	Si	14	1414	3265
Silver	Ag	47	961.78	2162
Sodium	Na	11	97.80	883
Strontium	Sr	38	777	1377
Sulphur	S	16	115.21	444.61
Tantalum	Ta	73	3017	5455
Technetium	Tc	43	2157	4262
Tellurium	Te	52	449.51	988
Tennesine	Ts	117		
Terbium	Tb	65	1359	3230
Thallium	Tl	81	304	1473
Thorium	Th	90	1750	4788
Thulium	Tm	69	1545	1950
Tin	Sn	50	231.93	2602
Titane	Ti	22	1668	3287
Tungsten	W	74	3422	5555
Uranium	U	92	1135	4131
Vanadium	V	23	1910	3407
Xenon	Xe	54	-111.74	-108.09
Ytterbium	Yb	70	824	1196
Yttrium	Y	39	1522	3345
Zinc	Zn	30	419	907
Zirconium	Zr	40	1855	4409